# CONTROLS (UK) LTD



Fine Controls have been supplying process controls & instrumentation equipment since 1994, & now serves an ever expanding customer base, both in the UK & globally.

We offer a full range of valve & instrumentation products & services, with our product rangerepresenting leading technologies & brands:

**Flow:** Flow Meters & Transmitters, Flow Switches, Flow Control Valves & Batch Control Systems

**Temperature:** Temperature Probes & Thermowells, Temperature ransmitters, Temperature Regulators & Temperature Displays

Level: Level Transmitters & Switches

**Pressure:** Pressure Gauges & Transmitters, Precision & High Pressure Regulators & I-P Converters, Volume boosters.

**Precision Pneumatics:** Pressure Regulators, I-P Converters, Volume Boosters, Vacuum Regulators

**Valves:** Solenoid & Pneumatic Valves, Control Valves & Positioners, Actuated Ball, Globe or Diaphragm Valves & Isolation Valves

**Services:** Repair, Calibration, Panel Build, System Design & Commissioning





# burkert















## Honeywell












Fine Controls (UK) LTD, Bassendale Road, Croft Business Park, Bromborough, Wirral, CH62 3QL UK
Tel: 0151 343 9966
Email: sales@finecontrols.com



J Z Z





At Royal Unibrew in Faxe, Denmark, the compact SITRANS FC430 Coriolis flowmeter demonstrated superior measurement capabilities and performance stability in calculating the °Plato of unfermented beer.

### The customer

Headquarted in Faxe, Denmark, Royal Unibrew produces, markets, sells and distributes a variety of beverages including beer, malt, soft drinks, fruit juices and mineral water. The brewery has a leading presence in a number of markets throughout Western and Eastern Europe, the Caribbean, Africa and North America.

In 2010, Royal Unibrew posted revenue of DKK 3.8 billion and sold 6.6 hectoliters of beverage. The brewery, which currently employs approximately 2,200 people, has undergone significant expansion in recent years, including the addition of a fully automated multi-storey warehouse with room for 18,500 pallets.

### The challenge

Producing beer that demonstrates uniform taste, color and consistency is one of the biggest and most important challenges faced by any brewery. Although the brewing cycle generally only lasts for several weeks, it involves many steps that

### The case at a glance

Region: Denmark

Industry: Food & Beverage

Customer: Royal Unibrew

**Challenge:** Ensure consistent product quality through accurate measurement of sugar concentration in wort prior to fermentation.

**Product: SITRANS FC430** 

### Main benefits:

- Real-time °Plato measurement
- Stable performance in dynamic flow and temperature conditions
- Most compact Coriolis solution on the market
- Digital signal reduces noise interference and enhances accuracy



The field test setup, consisting of two existing Siemens Coriolis meters and the new SITRANS FC430.



The whirlpool, where solid materials are separated out from the wort prior to fermentation.

must be regulated through repeated measurements to ensure that the beer will adhere to a predetermined standard of quality.

Accurate measurement becomes especially critical after the wort (unfermented beer) is boiled in the brewkettle with hops and other additives, which causes some proteins to denature and coagulate. When the boil is complete, the wort is transferred at a high velocity to the whirlpool vessel, which forces much of the solid material to separate and settle into a cone shape at the center of the tank. Before the wort is moved from the whirlpool to the wort cooler to be prepared for fermentation, the concentration of sugar in the wort must be quantified to enable a calculation of the brewhouse yield.

### The solution

Royal Unibrew has utilized several types of SITRANS F flowmeters from Siemens to regulate all aspects of the brewing process for more than a decade, including SITRANS F C Coriolis meters to monitor the sugar concentration in wort prior to fermentation. The SITRANS F C meters measure the density and temperature of the flowing liquid and use a preprogrammed algorithm to calculate °Plato, which expresses the density of wort as the percentage of sugar by weight.

Because the brewery is highly satisfied with the products and customer support they have received from Siemens over the past 10 years, they agreed to participate in a field test conducted by Siemens for the next generation of Coriolis flowmeter: the SITRANS FC430. In addition to being the most compact flowmeter of its kind available on the market, the SITRANS FC430 is the first Coriolis meter from Siemens to utilize a digital signal for reduced noise interference.

To perform the field test, a SITRANS FC430 was installed adjacent to the whirlpool to measure outbound wort. This location was considered ideal for testing the stability of the meter due to constantly fluctuating flow rates and temperatures.

The existing Coriolis meters were left in place to serve as reference points. The SITRANS FC430 was then subject to a rigorous series of assessments that were carried out multiple times over an 8-month period.

The results showed that the SITRANS FC430 met or exceeded expectations in nearly all areas of examination. Findings included:

- Performance remained stable at zero flow, with a deviation between Auto Zero setting results no greater than 0.2% over the course of 10 tests
- Flow readings remained consistent over 4 consecutive days, demonstrating that the SITRANS FC430 performs as reliably as the older meters in long-running scenarios
- Mass and density readings were more accurate than the older meters under dynamic flow conditions, and comparably accurate under stable conditions
- Temperature readings were comparably accurate to the older meters under both stable and dynamic temperature conditions

Royal Unibrew is pleased with the results of the field test and believes that the SITRANS FC430 shows great potential due to its conveniently small size and exceptional functionalities. According to Jakob Agerbo Bach, maintenance manager at Royal Unibrew, "The SITRANS FC430 provides density and temperature readings accurately, reliably and with good response times, which is exactly what our brewery needs. We absolutely feel confident in the new generation of Coriolis flow technology from Siemens."

Date: January 2012

Siemens A/S Flow Instruments DK-6430 NORDBORG

Headquarter: Siemens A/S DK-2750 BALLERUP